

3 mm LED superbright white**1.90.690.295/0000****Electrical characteristics of LED**

Forward voltage typ. U_F at I_F	3.6 V/20 mA V
LED breakdown voltage U_R bei I_F	5V
Max. current, I_F	30 mA

Other specifications

Ambient temp. operating max.	+80 °C
Ambient temp. operating min.	-30 °C
Colour	white
Socket	without socket