

**LED BA 9s (MBC/MCC) superbright, green, 24 V**
**1.90.690.342/0000**

**Electrical characteristics of LED**

Forward voltage typ. $U_F$ at $I_F$	24 V
LED type	---
LED breakdown voltage $U_R$ bei $I_F$	24
Light current typ. $f_v/I_F$	---
Light intensity	1000 mcd
Max. current, $I_F$	15 mA
Current reduction from $T_0 = 50\text{ °C}$	---
Wavelength typ.	525 nm

**Other specifications**

Ambient temp. operating max.	+65 °C
Ambient temp. operating min.	-30 °C
Colour	green
Storage temperature max.	---
Storage temperature min.	---
Operating life	---
Socket	BA 9 s