

RAFIX 22 QR lamp socket, screw terminals, without coupling
5.00.070.074/0000

Dimensions

Width	10 mm
Mounting depth without cable	56.4 mm
Height	39.5 mm
Length	46 mm

Lamp characteristics

Operating voltage AC/DC	6 ... 250 V
Lamp socket	BA 9 s
Lamp power max.	2 W
Lamp voltage	6 ... 250 V

Mechanical design

Terminal marking	X1 = anode, X2 = cathode
Terminals	screw terminals
Mounting	snap on coupling and actuator
Diode and resistor	no

Other specifications

Approvals	ENEC 10/15; ULc
Ambient temp. operating max.	+70 (+65 with LED) °C
Ambient temp. operating min.	-25 °C
Flame class acc. to UL 94	V 0
Hot wire ignition acc. to IEC 60695-2-1	yes
Resistance to constant environment	IEC 600 68-2-3 and 2-30
Storage temperature max.	+80 °C
Storage temperature min.	-40 °C
Robustness	acc. IEC 60947-5-5
Shock resistance acc. to IEC 600 68-2-27	50 g at 11 ms, amplitude half sinusoidal
Resistance to vibrations acc. to IEC 600 68-2-6	10 g at 40 ... 500 Hz
Resistance at variable environment	IEC 600 68-2-14 and 2-33