



[Cherry Home](#)
[Keyboards Home](#)
[Point of Sale Keyboards](#)
[Integrated Security Devices](#)
[Government Security Devices](#)
[Industrial / eHEALTH Keyboards](#)
[Office Products](#)
[Find A Rep or Distributor](#)
[Request Quotation](#)
[Ask A Question](#)
[Request A Catalog](#)
[Software Download](#)
[FAQs](#)



Check Distributor Stock

 Text Search

 Product Series Search

Follow Cherry on
Twitter and Facebook



G83-6104 Business Keyboard

Desktop Products



Reliable PC Business Keyboard with Proven Performance



[Download G83-6104
Business Keyboard
Datasheet pdf](#)

[Download Software](#)

Features

- 104 or 105 keys (depending on international layout)
- USB version available with a bus-powered hub for the connection of up to 4 other USB devices.
- Space-efficient compact layout
- Membrane contact switches with rubber-mat technology for individual use
- Reliability:
MCBF = 1 x 10⁹ operations;
MTBF > 80 000 hours
- Operating life of individual keys read to more than 20 million operations
- Keycap symbols are wear-resistant and easy to clean

Main Part Numbers

G83-6104LPNEU-0
 Light Grey, PS/2, 104 Key layout

G83-6104LPNEU-2
 Black, PS/2, 104 Key layout

G83-6104LNEU-0
 Light Grey, USB, 104 Key layout

G83-6104LNEU-2
 Black, USB, 104 Key layout

International Layout Codes

(1) US Layouts
 US English (US)
 EU English (US) with €

(2) European Layouts
 BE Belgian
 CH Swiss
 DE German
 DK Danish
 ES Spanish
 FR French
 GB English (UK)
 IT Italian
 NO Norwegian
 PO Portuguese
 SF Swedish/Finnish

Other versions available on request.

Color Codes
 -0 Grey housing Grey keys
 -2 Black housing Black keys

*Only for G83-6104 LRN and G83-6105 LRN available

Technical Data

Power Supply
 PS/2 Interface:
 +5 V/DC ± 5%

 USB Interface:
 min +4.15 V/DC, max +5.25 V/DC

 USB hub
 min +4.75 V/DC, max +5.25 V/DC

Current Input
 Interface:
 PS/2: max. 35 mA
 USB: typ. 500 mA
 USB hub: typ. 100 mA

Travel
 Total travel: 3.7 mm
 Pretravel: 2.4 mm
 Actuation force: 60 cN

Connecting Cable
 approx. 1.75 m

Weight
 approx. 1.190 g

Dimensions
 458 x 170 x 42 mm (keyboard)
 approx. 458 x 195 x 42 mm (with USB hub)

Storage Temperature
 -20 °C to 60 °C

Operating Temperature
 0 °C to 50 °C

Technical Support
 For information on repairs or warranty status contact:
 Cherry Technical Support
 Phone: 800.510.1689
 E-Mail: keyboardsupport@zf.com