


MATERIAL: ALUMINUM
 COVER: .040 THK (1.02mm)
 CHASSIS: .063 THK (1.60mm)



0.1666 - 4 PL
 (.175 [4.45mm] MAX.
 SCREW PENETRATION)

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		APPROVALS	DATE	CONDOR D.C. POWER SUPPLIES SUBSIDIARY OF ST. INDUSTRIES OXNARD, CALIF. 93033 (805) 486-4565
20635	A	JO	11/19/02	
ECO #	REV.	DESCRIPTION	DATE	REV.
		RELEASE	12/2/02	R.R. APPROVED
DO NOT SCALE DRAWINGS				
THIS DRAWING AND SPECIFICATIONS HEREAFTER THE PROPERTY OF CONDOR DO NOT BE LOANED, REPRODUCED, COPIED, OR IN ANY MANNER DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN PERMISSION OF CONDOR.				
MATERIAL		FINISH	APPRO	SCALE
				C
				SIZE
				DWG. NO.
				34-30466-0050
				SEE DWG# & REV
				SHEET 1 OF 1