



site search:
Home | C³-Distributor Log In | Cooper Industries | Contact Us



[Electrical UL/CSA](#) | [Electrical IEC](#) | [Electronics](#) | [Consumer/Aftermarket](#) | [OEM Transportation](#) | [Wireless](#) | [Systems/Services/Software](#)

Cooper Bussmann

CTX02-15242

REPL BY: CTX02-15242-R

- [Homepage](#)
- [About Cooper Bussmann](#)
- [Contact Us](#)
- [Privacy](#)
- [Legal](#)
- [Cooper Bussmann® Brand](#)
- [Site Map](#)

Product Information

Product Type: Inductor
 Product Family: Magnetics
 Product Series: Default-Inductor
 Brand: Coiltronics

Physical Properties

Dimensions: 22.3in.(L) × 17.1in.(W) × 8.4in.(H)
 Package Quantity: 200
 Number of Terminals, Pins, or Leads: 12

Mechanical Properties

Frequencies: Minimum: 200000
 Nominal: 275000

Electrical Properties

Input Voltages: Minimum: 36
 Nominal: 48
 Maximum: 72
 Open Circuit Inductance: 97.1
 Output Power: 13