

GENERAL LAYOUT INFO

The diagram illustrates the general layout of a component array. It features a 4x6 grid of components, each represented by a semi-circular shape with a horizontal line through its center. The components are arranged in two rows of three on the left and two rows of three on the right, separated by a vertical dashed line. The entire array is enclosed in an orange rectangular border. Four orange circles are positioned at the corners of the array: top-left, top-right, bottom-left, and bottom-right. Dimension lines indicate the spacing between the components. A horizontal dimension line at the top shows a distance of 23.5 ± 0.2 between the centers of the first and second components in the top row. A vertical dimension line on the left shows a distance of 23.5 ± 0.2 between the centers of the first and second components in the first column. A horizontal dashed line runs through the center of the array, and a vertical dashed line runs through the center of the array.

NOTES:

- TAPE SPEC: 3M 9495LE
- THICKNESS 0.17mm
- GENERAL OFFSET FROM HOLDER EDGES IS 0.2mm

SCALE 1:2

Sheet 10 of 10

 103 BUCKINGHAM AVE, SLOUGH, BERKSHIRE, SL1 4PF, UK Tel: +44 1753 610800, Fax: +44 1753 611359 Email: design@carclo-optics.com www.carclo-optics.com		Title		UNIVERSAL SHEET ADHESIVE PAD ASSEMBLY					
		Customer		CARCLO					
		Drawn by		FP	Material	SEE NOTE		Scale	AS SPEC.
THIRD ANGLE PROJECTION		GENERAL TOLERANCES UNLESS OTHERWISE STATED			DIMENSIONS IN mm		Format Size		A3
		CARCLO technical plastics CONFIDENTIAL: UNAUTHORISED COPYING, DISCUSSION & DISTRIBUTION PROHIBITED			CAD File		80-12567-70064-UNI-SHEET-PAD		
					Drw. N°		70064	Part N°	
0 ± 0.25 0 ± 1° 0.0 ± 0.1 0.0 ± 0.5° 0.00 ± 0.05 0.00 ± 0.1°									

SCALE 1:2

 103 BUCKINGHAM AVE, SLOUGH, BERKSHIRE, SL1 4PF, UK Tel: +44 1753 610800, Fax: +44 1753 811359 Email: design@carclo-optics.com www.carclo-optics.com		Title		UNIVERSAL SHEET ADHESIVE PAD ASSEMBLY																
		Customer		CARCLO																
		Drawn by	FP	Material	SEE NOTE			Scale	AS SPEC.											
 THIRD ANGLE PROJECTION		GENERAL TOLERANCES UNLESS OTHERWISE STATED <table border="1"> <thead> <tr> <th colspan="2">LINEAR</th> <th colspan="2">ANGULAR</th> </tr> </thead> <tbody> <tr> <td>0 ± 0.25</td> <td>0 ± 1°</td> </tr> <tr> <td>0.0 ± 0.1</td> <td>0.0 ± 0.5°</td> </tr> <tr> <td>0.00 ± 0.05</td> <td>0.00 ± 0.1°</td> </tr> </tbody> </table>		LINEAR		ANGULAR		0 ± 0.25	0 ± 1°	0.0 ± 0.1	0.0 ± 0.5°	0.00 ± 0.05	0.00 ± 0.1°	CARCLO technical plastics CONFIDENTIAL: UNAUTHORISED COPYING, DISCUSSION & DISTRIBUTION PROHIBITED		DIMENSIONS IN mm		Format Size		A3
				LINEAR		ANGULAR														
				0 ± 0.25	0 ± 1°															
0.0 ± 0.1	0.0 ± 0.5°																			
0.00 ± 0.05	0.00 ± 0.1°																			
CAD File	80-12567-70064-UNI-SHEET-PAD																			
Drw. N°	70064		Part N°	12567																