


Specifications			Notes	Revision History					
Description	Value	Unit		Version	Description	Date	Approved		
Shape	Rectangle		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS <div style="text-align: center; margin-top: 20px;">   <b>DB UNLIMITED</b> </div>	1	Released from Engineering	10/21/2013	J.S		
Resonant Frequency	300	(Hz)							
Frequency Range	300 ~ 20,000	(Hz)							
SPL @ 10cm	86	(dBA)							
Impedance	8	(Ohm)							
Cone Material	Mylar								
Nominal Power	12	(W)							
Max Power	15	(W)							
Mount Type	Frame								
Operating Temperature	-25 ~ +55	°C							
Storage Temperature	-25 ~ +55	°C							
Weight	250	(g)							
			<b>Dynamic Speaker</b>	<b>SM830308-1</b>					
				Drawn by	Date	Checked by	Date	Approved by	Date
				A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013