



[Request more info](#)

Part Number : 5973231207F



5973231207F



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	597
Configuration	PLCC-2
Description	SMD LED PLCC A 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
LED Type	AllnGaP
Lens Color	Non-Diffused

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	30mA
Forward Current Pulsed	100mA
Derating	from 75° @ .8mA/°C
Solder Temperature	235° for 15 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

Operating Characteristics

Color	Amber
Luminous Intensity Min	20
Luminous Intensity Typical	80
Test Current mA	-
Power Dissipation Max	70mW