




REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	KLJ	NO		10-17-08

CHARMILLE #18
FINISH ON FRONT
SURFACE ONLY




RIBS FOR
PRESS-FIT
(3 PLCS)


LIGHT PIPE
FLUSH WITH
PANEL



RECOMMENDED PANEL DIMENSIONS
FOR FLUSH MOUNT INSTALLATION



RECOMMENDED PANEL DIMENSIONS
FOR PROTRUDED INSTALLATION
&
RECOMMENDED LED PLACEMENT



NOTES:

- COMPONENTS MOLDED IN A CLEAR TRANSMISSIVE POLYCARBONATE (UL 94V-0 FLAMMABILITY CLASS).
- COMPONENTS DESIGNED TO BE PRESSED INTO FRONT PANEL.
- RECOMMENDED LIGHT SOURCES: SMT LED (0603, 0805, AND 1206 PACKAGE SIZES)
- MOUNTING HOLE SIZE: Ø.035±.002 (#65 DRILL)
- DIALIGHT PART NUMBER: 515-1016F

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT CORP. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT CORP.		
SCALE: 14.000 ALL DIM's: INCH (mm)	DRAWING NUMBER C-17664	REV A
TOLERANCES: UNLESS OTHERWISE SPECIFIED FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005 DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	TITLE Ø.064 STRAIGHT LIGHT PIPE W/ PRESS-FIT; RoHS COMPLIANT	
FINISH -	MATERIAL -	
FSCM 83330	SHEET 1 OF 1 FAMILY TABLE:	

RoHS COMPLIANT 515-1016F

Part Numbers with the "F" suffix ending are RoHS Compliant.
Packaging is marked with "RoHS Compliant" label or equivalent markings.