<u>Diali</u>ght

Request more info

Part Number : 5520221F



5520221F



This is a RoHS Compliant Product To learn more click here

			Share	I	I
General Description					
Series	552				
Configuration	5 mm Lens				
Description	5 mm Bi-Level CBI				
Package Options	Bulk Packaging				
Sizes	5mm				
Lamp Type	Bi-Level Housing				
Viewing	Right Angle				
Polarity	Cathode Right				
Lens Style	Tinted, Diffused				
Viewing Angle	65				
LED Centerline	3.2mm				
Absolute Maximum Ratings (Ta = 25°)					
Solder Temperature	260 for 5 secs				
Operating Temperature	-25 to +85				
Storage Temperature	-30 to +100				
Operating Characteristics					
Peak Wave Length	650	563			
LED Position	1	2			
Luminous Intensity Min	2.2	3.6			
Luminous Intensity Typical	6.3	10			
Forward Voltage Typical	2.2	2.1			
Forward Voltage Max	2.55	3			
Test Current mA	10mA				

75mW

6.35

60mW

Pitch Between Vertical Power Dissipation Max