





REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	0	RELEASED	01/25/05	CC
	1	Changed wire colors	09/26/05	CC

H6815XXX	"L" (length)
076	3"
152	6"
229/230	9"
305	12"
457/460	18"
610	24"



- NOTES:
1. ALL WIRING MUST HAVE A FLAMMABILITY RATING EQUIVALENT TO UL-94V1 AND AN APPROPRIATE UL STYLE NUMBER
 2. CABLE INSULATION TO BE CAPTIVATED BY CRIMP TERMINAL, SEE IPC/WHMA-A-620 FOR ACCEPTABILITY.
 3. WIRES TO BE 26 AWG, MIL STD W16878 TYPE B (BELDEN #8504 OR EQUIVELANT) IN COLORS LISTED.
 4. CONNECTOR N22240 WIRE STRIP LENGTH IS 1.65 ± .25mm.

			
MATERIAL	APPROVALS	DATE	 ENDICOTT RESEARCH GROUP, INC. 2601 WAYNE ST., ENDICOTT, NY 13760 607-754-9187 WIRING HARNESS H6815
FINISH	DRAWN	01/25/05	
	CHECKED	01/25/05	
	APPROVED	01/25/05	REV
DO NOT SCALE	C	DRAWING NUMBER	H6815
	SCALE	SHEET	1 OF 1