

## Series 14002

### Specifications

**Description:** Barrier terminal block.

**Poles:** 2- to 6-poles.

**Wire Range:** 2 – 14 AWG Cu/8 AWG Al.

#### Ratings:

Volts: — 600Vac/dc

Amps: — 115A

SCCR:— 10kA per

UL 508A table SB4.1

**Agency Information:** CE, Guide XCFR2, UL E62622; CSA LR15364.

**Torque Ratings\*:** 2-3, 50 lb-in; 4-6, 45 lb-in; 8, 40 lb-in; 10-14, 35 lb-in.

\*Consult factory for torque ratings for CP and Q options.

**Marking:** Marking strip optional, consult factory.

#### Options For Load Side Connector

CP: Sems pressure plate, rated 60A, 600V

Q: Quick-Connect, rated 50A, 600V

To order options, enter letter code in front of Catalog Number: i.e., CP14002-2.

#### Catalog Numbers

Catalog Numbers	Poles	Catalog Numbers	Poles
14002-2	2	14002-5	5
14002-3	3	14002-6	6
14002-4	4		

