



Plastic Non Threaded Spacer - 2.3 mm | 0.091 in ; 4.8 mm | 0.188 in ; 11.1 mm | 0.438 in

This is a Round Natural Nylon 6/6 non-threaded spacer. It has a 0.091 in inside diameter and a 0.188 in outside diameter. The spacer length is 0.438 in Replaces Item No.(s): SWS0060A

Item code: **13SP011**

● 48900 In stock

Quantity	Unit price
1000 - 9999	\$0.0627
10000 - 24999	\$0.0549
25000+	\$0.0471

Total price: **\$62.70**
1000 x
\$0.0627

Quantity

Standard pack: 1000
Order in multiple of 1000

Add to cart

Add item to list

[Download CAD](#)

[Request a quote](#)

Specifications

Inside Diameter	0.091 in
Outside Diameter	0.188 in
Spacer Length	0.438 in
Color	Natural
Full Material	Nylon 6/6
Material	Nylon
Material Flammability Standard	UL94 V-2
Spacer Shape	Round

Legislation & Compliance

