



NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
COLOR: NATURAL
2. FOR T-1 3/4 LED'S.

PART NUMBER	"L" ±.010 (±0.25)	"A" REF.
LEDS2M-.120-01	.12 (3.1)	.08 (2.0)
LEDS2M-.140-01	.14 (3.6)	
LEDS2M-.160-01	.16 (4.1)	
LEDS2M-.180-01	.18 (4.5)	
LEDS2M-.200-01	.20 (5.1)	
LEDS2M-.220-01	.22 (5.6)	
LEDS2M-.240-01	.24 (6.1)	.20 (5.1)
LEDS2M-.250-01	.25 (6.4)	
LEDS2M-.260-01	.26 (6.6)	
LEDS2M-.280-01	.28 (7.1)	
LEDS2M-.300-01	.30 (7.8)	
LEDS2M-.340-01	.34 (8.6)	
LEDS2M-.360-01	.36 (9.1)	.33 (8.4)
LEDS2M-.380-01	.38 (9.7)	
LEDS2M-.400-01	.40 (10.2)	
LEDS2M-.420-01	.42 (10.7)	
LEDS2M-.450-01	.45 (11.4)	
LEDS2M-.460-01	.46 (11.7)	.45 (11.4)
LEDS2M-.550-01	.55 (14.0)	
LEDS2M-.600-01	.60 (15.2)	.58 (14.7)
LEDS2M-.650-01	.65 (16.5)	
LEDS2M-.850-01	.85 (21.6)	.70 (17.8)
LEDS2M-.900-01	.90 (22.9)	

2. FOR 1-1 3/4 LED S.			TITLE: LED SPACER						DWG IN IN (MM)	
F	SEE ECN #1168 FOR CHANGES	SK 05.19.06	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE #	LEDS2M	DWN: D.D.	APP:	FINAL		
E	SEE ECN #892 FOR CHANGES	SM 12.14.04		MAT'L: SEE NOTES		DT: 05-20-96	DT:	PART #		
D	SEE ECN #547 FOR CHANGES	SM 12.20.02		RE: RICHCO, INC.		RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539-4060		SEE TABLE		
C	SEE ECN #526 FOR CHANGES	SM 11.21.02						PRINT TYPE		
B	CHANGED DIM "A" (SEE ENGINEERING)	SM 11.01.01						CA		
A	CHANGED FILE NO. AND TITLE BLOCK	SM 10.03.01								
REV	DESCRIPTION	ENGR DATE								

TOLERANCES
UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

FILE # LEDS2M
MAT'L: SEE NOTES
RE: RICHCO, INC.

DWN: D.D.
DT: 05-20-96
APP:
RICHCO INC.
PO BOX 804238, CHICAGO, 60680
(773) 539-4060