



PART NO.	DIM. "A"
OFFGSP-R-05-19-BK	.20 [5.0]
OFFGSP-R-10-19-BK	.39 [10.0]
OFFGSP-R-16-19-BK	.63 [16.0]



TO SNAP-LOCK INTO A $\phi .098 \pm .002$
[2.5 ± 0.05] HOLE, IN A .063 [1.6]
BOARD THICKNESS

NOTES:

1. MATERIAL: FLAME RETARDAN NYLON 6/6 (RMS-19).
2. COLOR: BLACK.

B	SEE ECN #924 FOR CHANGES	SK	01/25/05
A	RELEASED FOR PRODUCTION	SM	08/13/04
REV.	DESCRIPTION	ENGR.	DATE

TITLE: FLEXIBLE FIBER GUIDE SUPPORT POST							DWG IN IN [MM]	
CREATED USING SOLIDWORKS	FILE #: OFFGSP-R		DWN: SM	APP: DJZ	FINAL			
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: A	DT: 08/13/04	CHKD: SJ	PART #		PRINT TYPE	
	RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		SEE TABLE		CA	