



White PA Snap-In Bearing Sleeve Bearing - ; Overall Length 2 mm | 0.078 in

This Sleeve Bearing supports a rotating shaft while efficiently dampening noise and vibration, allowing for smooth rotational movement. Impermeable to dirt ingress and corrosion, with an axiam slot that maintains proper fit. It has a maximum shaft of 3/16 in, and withstands temperatures of -40F to +200F.



Item code: **R3L1-C** 

## Specifications

Imperial  Metric

Nominal Inside Diameter	0.189 in
Nominal Outside Diameter	0.188 in
Overall Length	0.078 in
Overall Diameter	0.188 in
Material	PA
Full Material	Nylon 6/6
Bearing Material	Nylon
Bearing Type	Snap-In Bearing
Material Flammability Standard	UL94 V-2
Measurement Standard	Imperial
Color	White