

1:3

NOTE

MATERIAL : C1008 STEEL
 FINISH : BRIGHT NICKEL CHROME PLATED

APPROVED - UNCONTROLLED

UNLESS OTHERWISE STATED


ALL DIMENSIONS IN mm

DO NOT SCALE

LINEAR TOLERANCE

SIZE	(0)	(0.0)	(0.00)
0-10mm	±0.5	±0.15	±0.10
>10-30	±0.5	±0.20	±0.15
>30-50	±0.5	±0.30	±0.20
>50-100	±0.8	±0.50	±0.25
>100-200	±1.5	±0.80	±0.40
>200-300	±2.0	±1.20	±0.80
>300-500	±3.0	±2.00	±1.00
>500	±5.0	±3.00	±1.50

THIRD ANGLE PROJECTION



ANGULAR TOLERANCE ±0.5 DEGREES
 UNSPECIFIED RADII 0.25mm
 DRAFT ANGLE 0.5 DEGREES
 DIMENSIONS IN BRACKETS [] ARE
 IN INCHES FOR REFERENCE ONLY

ORG. SCALE: 1:2

CREATE DATE: 08/05/2019

MATERIAL: SEE NOTES

Part ID: 1127563

Project: P160066-1

TITLE: FAN GUARD

DWG. No.

RCOFM-120

SHEET
1 of 1
ISSUE
2