



Natural Nylon Anti-Loss Retaining Washer - 4.3 mm
| 0.169 in; 7.0 mm | 0.276 in; Thickness 2.3 mm |
0.091 in; Compatible Screw Sizes M4

Item code: RWM200A ● 13000 In stock

Retaining Washer made from Nylon and featuring a 7.0 mm | 0.276 in Outside Diameter, 4.3 mm | 0.169 in Inside Diameter and 2.3 mm | 0.091 in Thickness. This item is compatible with M4 screws sizes.

[See all specs and customize](#) ↓

Cookies on Essentra Components US

Cookie consent - by continuing to browse or by clicking 'Accept', you agree to the storing of cookies on your device to enhance your site experience and for analytical purposes.

To learn more about how we use the cookies, please see our cookie policy.

Accept

Standard pack: 1000
Order in multiple of 1000

Quantity

1

Total price:
\$0.51
1 x **\$0.5061**

Quantity	Unit price
1 - 99	\$0.5061
100 - 499	\$0.2293
500 - 999	\$0.1614
1000 - 4999	\$0.0917
5000 - 9999	\$0.0872
10000 - 14999	\$0.0826
15000+	\$0.078

Add to cart

+ [Add item to list](#)

Need a quote?

For large volumes and customized products, add to your cart and click request a quote, or email sales@essentracomponents.com and we will respond within 2 working days.

Can't find what you're looking for?
Tell us what you are looking for...

Send us your inquiry and we'll get back to you in 24 hours.

Contact us

Request a quote

Specifications

Inside Diameter	0.169 in
Outside Diameter	0.276 in
Thickness	0.091 in
Color	Natural
Compatible Screw Sizes (All)	M4
Material	Nylon
Full Material	Nylon 6/6
Washer Type	Anti-Loss
Washer Shape	Round
Tooth Location	Internal

Recently viewed items



Natural Nylon Anti-Loss Retaining Washer - 4.3 mm | 0.169 in; 7.0 mm | 0.276 in; Thickness 2.3 m...

[See our selection](#) →



Twist Tie - Fir Tree ; Nylon ; Compatible Cable Diameter Range - 7.6 - 10.2 mm | .30 - .40 in

[See our selection](#) →