




PART NO.	THREAD TYPE
TB-1	#6-32
TB-2	#8-32
TB-3	M3
TB-4	M4



NOTES:

1. MATERIAL: RUBBER BUMPER - IIR, SHORE 40-50A DUROMETER (RMS-348)
THREADED STEM - BRASS (RMS-349)
2. COLOR: RUBBER BUMPER - BLACK
THREADED STEM - AS MACHINED
3. TYPICAL COMPRESSION FOR 10 LB MAX LOAD = .03 [0.8]

				TITLE: THREADED BUMPERS						DWG IN IN[MM]							
				CREATED USING SOLIDWORKS		FILE #: TB		DWN: S.J.		APP: S.J.		FINAL					
				TOLERANCES UNLESS NOTED		SHEET: 1 OF 1		SHEET SIZE: A		DT: 1.09.07		CHKD: S.K.		PART #		PRINT TYPE	
B		SEE ECN #1309 FOR CHANGES		SK 04/05/07		RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		SEE TABLE						CA	
A		RELEASED FOR PRODUCTION		SK 01/09/07													
REV.		DESCRIPTION		ENGR. DATE													