



A		B		C		D		E		F		G		H	
PART NO.	MIN. LOOP TENSILE Kg [lbs]	'L' (REF)	'A'	'B' (REF)	'C' (REF)	'D' (REF)	'T'	'W'	HOLE DIA. ±0.08 [.003]	MAX BUNDLE DIAMETER					
WIT-30RRAA-16	13 [30]	180.7 [7.114]	7.9 [.311]	14.3 [.562]	25.4 [1.00]	6.6 [.259]	1.3 [.051]	3.6 [.141]	6.35 [.250]	31.8 [1.250]					
WIT-30RRAA-12	13 [30]	174.3 [6.862]	7.9 [.311]	14.3 [.562]	19.8 [.779]	6.6 [.259]	1.3 [.051]	3.6 [.141]	6.35 [.250]	31.8 [1.250]					
WIT-30RRAA-8	13 [30]	168.0 [6.614]	7.9 [.311]	14.3 [.562]	13.5 [.531]	6.6 [.259]	1.3 [.051]	3.6 [.141]	6.35 [.250]	31.8 [1.250]					
WIT-30RRAA-4	13 [30]	161.6 [6.362]	7.9 [.311]	14.3 [.562]	7.1 [.279]	6.6 [.259]	1.3 [.051]	3.6 [.141]	6.35 [.250]	31.8 [1.250]					
WIT-30RRA-16	13 [30]	179.4 [7.062]	7.1 [.279]	14.3 [.562]	25.4 [1.00]	5.3 [.210]	1.3 [.051]	3.6 [.141]	4.8 [.187]	31.8 [1.250]					
WIT-30RRA-12	13 [30]	173.0 [6.812]	7.1 [.279]	14.3 [.562]	19.8 [.779]	5.3 [.210]	1.3 [.051]	3.6 [.141]	4.8 [.187]	31.8 [1.250]					
WIT-30RRA-8	13 [30]	166.7 [6.562]	7.1 [.279]	14.3 [.562]	13.5 [.531]	5.3 [.210]	1.3 [.051]	3.6 [.141]	4.8 [.187]	31.8 [1.250]					
WIT-30RRA-4	13 [30]	160.3 [6.312]	7.1 [.279]	14.3 [.562]	7.1 [.279]	5.3 [.210]	1.3 [.051]	3.6 [.141]	4.8 [.187]	31.8 [1.250]					

RELEASE TAB



1 COLLAR ON SIZE 4 ONLY



NOTES:

- PANEL THICKNESS: 0.8-2.0 [.030-.078]
- OTHER MATERIALS AVAILABLE BY SPECIAL ORDER. ADD '-HS', '-V0', '-UVB' OR '-HT' BEFORE '-M' IN THE PART NUMBER. EXAMPLE: WIT-30RRA-4-V0-M.
 - HEAT STABILIZED NYLON 6/6, UL94 V-2, RMS-47, COLOUR: BLACK
 - NYLON 6/6, UL94 V-0, RMS-19, COLOUR: NATURAL
 - UVB STABILIZED NYLON 6/6 UL94 V-2, RMS-46, COLOUR: BLACK
 - NYLON 6/6, UL94 V-2, RMS-01, COLOUR: BLACK
 - HIGH TEMPERATURE NYLON 4/6 UL94 V-2, RMS-109, COLOUR: NATURAL

09	CO-2010582	26/02/09	TC
08	CO-2010232	14/05/08	SF
07	CO-2010215	08/05/08	SF
06	CO-2010212	07/05/08	SF
05	CO-2010178	09/04/08	MT
REV	MODIFICATION	DATE	DRN

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.			
		METRIC PRIMARY UNITS: mm IMPERIAL SECONDARY UNITS [inches] GENERAL TOLERANCES ±0.25 [0.010] UNLESS OTHERWISE STATED 1 DECIMAL PLACE ± 0.25 2 DECIMAL PLACES ± 0.1 ANGULAR ±1°	
MATERIAL: NYLON 6/6 UL94-V2 (RMS-01)		COLOUR: NATURAL	
DESCRIPTION: WIT-30RRA(A) Releasable Self-Mount Ties.		PART No: SEE TABLE	
DRG No: 07-001	NPR No: 2006-303	Mass:(g)	SHEET SIZE A3
DRN NJB	DATE 05/01/07	CHKD TC	DATE 05/01/07
SCALE NTS		SHEET No. 1 OF 1	