



PCB Support - Locking Teardrop ; Spacer Length 10.0 mm | 0.394 in ; Style 2

Item code: **MDLSP2-10M-01**

● In production

This double locking circuit board support allows to firmly stack two boards at the desired distance without the need of extra tools, saving on assembly times. This support is manufactured with material rated UL94 V-2.



Order sample

[Download CAD](#)

[Add sample +](#)

Total price **0.13**
USD

1 x
0.1312
USD

Quantity

Standard pack: 1000
Order in multiple of 1000

Quantities	
1 - 999	Add to cart
1000 - 9999	Add item to list
10000 - 39999	
40000+ i	Need a quote? 0.0676 USD

**Can't find what
you're looking
for?
Tell us what you
are looking for...**

Send us your enquiry and we will aim to get back to you within 2 working days

Contact us

Request a quote

Specifications

Colour	Natural
Hole A Fix Type	Locking Teardrop
Hole B Fix Type	Locking Teardrop
Material	Nylon
Body Diameter	4.6 mm
Hole Diameter A	3.5 mm
Hole Diameter B	3.5 mm
Locking Head Height A	3.5 mm
Locking Head Height B	3.5 mm
Maximum Operating Temperature	85 °C
Maximum Panel Thickness A	1.65 mm
Maximum Panel Thickness B	1.65 mm
Minimum Operating Temperature	-40 °C
Spacer Length	10.0 mm
Full Material	Nylon 6/6
Material Flammability Standard	UL94 V-2

Recently Viewed Items



**PCB Support - Locking
Teardrop ; Spacer Length
10.0 mm | 0.394 in ; Style 2**

[See our selection](#) →