



PART NO.	"A" ±.020 (±0.5)	"B"	"C"	"D" REF.	LED TYPE
SQLEDS1-4-26	.250 (6.4)	.17 (4.3)	.03 (0.8)	.17 (4.3)	T-1
SQLEDS1-6-26	.375 (9.5)				
SQLEDS1-8-26	.500 (12.7)				
SQLEDS2-4-26	.250 (6.4)	.24 (6.1)	.07 (1.8)	.27 (6.9)	T-13/4
SQLEDS2-6-26	.375 (9.5)				
SQLEDS2-8-26	.500 (12.7)				
SQLEDS2-10-26	.625 (15.9)				
SQLEDS2-12-26	.750 (19.1)				



TYPICAL APPLICATIONS



NOTES:

1. MATERIAL: PVC (RMS-26).
2. COLOR: BLACK.

TITLE: SQUARE LED SPACERS					DWG IN IN (MM)			
D	SEE ECN #1337 FOR CHANGES	SK 07.10.07	TOLERANCES UNLESS NOTED	FILE # SQLEDS	DWN: S.M.	APP:	PART # SEE TABLE	PRINT TYPE CA
C	REMOVED NOTE 2. AND LED 45° CUT	SM 03.23.01	.XX=±.010	MAT'L: SEE NOTES	DT: 03/12/01	DT:		
B	COMPLETELY RE-DRAWN	SM 03.12.01	.XXX=±.005	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060			
A	RELEASED TO PRODUCTION	SM 03.12.01	FRAC=±1/64					
REV	DESCRIPTION	ENGR DATE	ANG=±1°					