



NL668-EAU-00-MiniPCle-10 LTE Module

Perfect Wireless Experience

NL668-EAU-00-MiniPCle-10 LTE Module Technical Specifications

Product Feature

- LTE FDD: Band 1/3/5/7/8/20/28
- LTE TDD: Band 38/40/41
- WCDMA: Band 1/5/8
- GSM/GPRS/EDGE: 850/900/1800MHz
- MiniPCle: 51x30x4.9mm
- Operating Temperature: -30°C~+75°C
- Optional Operating Temperature: -40°C~+85°C
- Storage Temperature: -40°C~+85°C
- Operating Voltage: 3.3V~4.3V typical 3.8V
- **AT Command Set:** 3GPP TS 27.007 and 27.005, and proprietary FIBOCOM AT commands
- **TX Power**
 - GSM850: 32.5 dBm ± 1dB
 - GSM900: 32.5 dBm ± 1dB
 - DCS1800: 29.5dBm ± 1dB
 - WCDMA : 23.5dBm ± 1dB
 - LTE FDD: 23.0dBm ± 1dB
 - LTE TDD: 23.0dBm ± 1dB

Data

- LTE FDD: 150Mbps DL/50Mbps UL
- LTE TDD: 130Mbps DL/35Mbps UL
- UMTS: 384 kbps DL/384 kbps UL
- HSPA/HSPA+: 42Mbps DL/5.76Mbps UL
- EDGE: 296Kbps DL/236.8Kbps UL
- GPRS: 107Kbps DL/85.6Kbps UL
- MUX: Basic Mode
- SMS: MO/MT Text and PDU modes
- HTTP(S)/PPP/FTP(S)/TCP/UDP/TTS/SMTP/IPV4/IPV6
- ECM/RNDIS/Gobinet/NDIS
- DFOTA/FOAT
- eCall/SRLTE/VoLTE
- GNSS/LBS

Interface

- SIM Card: 1.8V/3.0V x 1
- USB 2.0 x 1
- UART x 1
- PCM/I2S x 1
- GPIO
- System Indicator
- Analog Audio
- Antenna: Main/Div/GNSS

Driver

- Linux/Android
- Win7/8/10

Approval

- CE-RED/GCF/RCM/Telstra/Anatel

Copyright © Fibocom Wireless Inc. | Subject to changes in technology, design and availability | E-mail : market@fibocom.com | Tel : +86 755-2673 3555