



RFCT-BNC-CAP-GS-2: METAL PROTECTIVE CAP WITH GASKET AND CHAIN FOR BNC JACK

Material and Plating:

1. Shell: Brass, nickel plated.
2. Gasket: Silicon, color: red.
3. Rivet: Brass, nickel plated.
4. Chain: Brass, nickel plated.
5. Joint: Stainless steel.

Notes:

1. Operating temperature: -40°C~+125°C.
2. Caps to be installed finger tight only. Do not overtighten.



REV.	DATE & DRN
10	17/05/19 - NYW RELEASE
11	08/01/20 - NYW ADD ENVIRONMENTAL INFO.
12	19/05/20 - NYW ADD ENVIRONMENTAL INFO.
13	18/06/20 - NYW REMOVED NAUTILUS RANGE.
14	06/08/20 - NYW ADD NOTE 1.
15	25/05/21 - NYW ADD NOTE 2.
16	15/07/23 - NYW ADD DEL LOGO.

Scale:	NTS	THIRD ANGLE	Unstated .X .XX .XXX ANGLES	Tolerances: ± 0.2 ± 0.2 ± 0.2 N/A
Drawn:	NYW			
App'd:	XXX	Title	BNC CAP	
Date:	12 MAY '25	Revision:	1.6	Unit: mm

www.gct.co	www.gradconn.com
THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT	

Type:	RFCT-BNC-CAP-GS-2
	RFCT-BNC-CAP-GS-2
Drawing Number:	
Sheet 1 of 1	
Drawing ©	E and O E