

Han Pneumatic module, for 1,6+ 3+ 4mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 003 4501
Specification	Han Pneumatic module, for 1,6+ 3+ 4mm
HARTING eCatalogue	https://b2b.harting.com/09140034501

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Pneumatic module

Version

Gender	Male Female
Number of contacts	3
Details	Please order contacts separately. Using of guiding pins is imperative!

Technical characteristics

Limiting temperature	-40 ... +80 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	2
Net weight	7 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440220 Module for industrial connectors (pneumatic)