

Han E M Crimp Contact Ag 1.0 mm²/ 18 AWG



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6105
Specification	Han E M Crimp Contact Ag 1.0 mm ² / 18 AWG
HARTING eCatalogue	https://b2b.harting.com/09330006105

Identification

Category	Contacts
Series	Han E [®]
Type of contact	Crimp contact

Version

Gender	Male
Contact identification	1 groove
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	1 mm ²
Conductor cross-section	AWG 18
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	f36aed3d-7511-4904-96d8-3efb28533423

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

Commercial data

Packaging size	100
Net weight	1.25 g
Country of origin	Switzerland
European customs tariff number	85366990
eCl@ss	27440204 Contact for industrial connectors