

Han E M Crimp Contact Ag 0.14-0.37 mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 33 000 6127
Specification	Han E M Crimp Contact Ag 0.14-0.37 mm ²
HARTING eCatalogue	https://b2b.harting.com/09330006127

Identification

Category	Contacts
Series	Han E [®]
Type of contact	Crimp contact

Version

Gender	Male
Contact identification	No groove
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.14 ... 0.37 mm ²
Conductor cross-section	AWG 26 ... AWG 22
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm
Mating cycles	≥500

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



Pushing Performance

Material properties

China RoHS 50

REACH Annex XVII substances No

REACH ANNEX XIV substances No

REACH SVHC substances Yes

REACH SVHC substances Lead

Specifications and approvals

Specifications EN 60664-1
IEC 61984

Commercial data

Packaging size 100

Net weight 1.21 g

Country of origin Switzerland

European customs tariff number 85366990

eCl@ss 27440204 Contact for industrial connectors