

PP-V14-PCB-THT-RJ45-8P-J-M-ANG-SHLD




Image is for illustration purposes only. Please refer to product description.

Part number	09 35 002 2101
Specification	PP-V14-PCB-THT-RJ45-8P-J-M-ANG-SHLD
HARTING eCatalogue	https://b2b.harting.com/09350022101

Identification

Category	Connectors
Series	Han [®] PushPull (V14)
Identification	RJ45
Element	Female
Specification	Angled With contact spring
Features	Intuitive locking mechanism

Version

Termination method	Wave soldering termination
Shielding	Fully shielded, 360° shielding contact
Pack contents	Tray

Technical characteristics

Rated current	1.75 A
Rated voltage	50 V
Transmission characteristics	Cat. 6
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s
Limiting temperature	-40 ... +85 °C
Mating cycles	≥750



Pushing Performance

Material properties

Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-3-117 Variant 14 (V14) IEC 60603-7 Mating face
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	360
Net weight	5.18 g
Country of origin	Japan
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors