

RJI RJ45 plug Cat5, 4p IDC




Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1100
Specification	RJI RJ45 plug Cat5, 4p IDC
HARTING eCatalogue	https://b2b.harting.com/09451511100

Identification

Category	Connectors
Series	HARTING RJ Industrial®
Element	Cable connector
Specification	Straight

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4
Pack contents	Hood with shielding Splicing element Cable gland Assembly instructions

Technical characteristics

Conductor cross-section	0.22 ... 0.32 mm ² Stranded 0.26 ... 0.32 mm ² Solid
Conductor cross-section	AWG 24 ... AWG 22 Stranded AWG 23 ... AWG 22 Solid
Wire outer diameter	≤1.6 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750



Pushing Performance

Technical characteristics

Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm
Vibration resistance	10-500 Hz, 10 g, 0.3 mm, 2h/axis 7.9 m/s ² acc. to IEC 61373 Category 1 Class B

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 60603-7 Mating face IEC 11801 EN 50173-1 EN 45545-2 R26: HL1, HL2, HL3
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	34.8 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)