


Dichtungseinsatz/sealing insert	
mit Inlet/with Inlet	ohne Inlet/without Inlet
min. $\phi 5$ , max. $\phi 9$	min. $\phi 9$ , max. $\phi 14$



All Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Masse/ Free size tolerances	
			Dat.	Name	Massstab/ Scale  <b>2:1</b>	<b>Verschraubung M20, Metall/ cable gland M20, metal</b>
			Detail.	07.03.07 ML		
			Insp.	Be		
			Stand.			
412547			HARTING Electric GmbH & Co. KG			<b>TB 19 00 000 5050</b>
Mod.	Dat.	Name	D-32339 Espelkamp			
						Blatt/ page Sub.