

## Han-Modular Compact top entry M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 14 001 0401
Specification	Han-Modular Compact top entry M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19140010401">https://b2b.harting.com/19140010401</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Modular® Compact
Type of hood/housing	Hood

### Version

Locking type	Single locking lever
Size	Modular Compact
Version	Top entry
Cable entry	1x M25
Details	<p>Rated voltage ≤630 V            Rated impulse voltage ≤6 kV            Pollution degree 3</p> <p>For a complete connector the specified voltage rating is the maximum level which can be achieved. In cases where the used module(s) do offer lower voltage ratings, then these lower ratings are valid. Higher voltage ratings in individual applications can be approved in coordination with HARTING.</p>
Pack contents	4 screws are included within the delivery

### Technical characteristics

Tightening torque	1 Nm Fixing screws M3
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 locked condition



Pushing Performance

## Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61984
CE	Yes

## Commercial data

Packaging size	10
Net weight	86 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors