

Part Number: POD-F-PR-1

POD(F) Series



-Features

- Floating structure in radial and mating direction enables multiple connectors fixed on a panel to mate at once.
- Unique push-on lock with "Top touch engagement", which top surfaces always touch preventing a gap, provides reliable high frequency characteristics.
- High frequency characteristics. V.S.W.R. 1.3 max., from DC to 12GHz.
- Environment-friendly without banned substance of RoHS.

Characteristic	Specifications
Contact Mating Area Plating	Gold
Impedance (ohm)	50
Operating Temperature Range (degrees C)	-40 to 85
Termination Style	Soldering
Connector Type	Panel
Contact Gender	Male
Mating/Unmating Cycles	500
VSWR (Max)	1.3

General Description:

Plug receptacle; Straight; Panel mounting with flange