



Regular Nyties

- Smooth, radiused edges ensure that Nyties won't cut into the cable's insulation—or the installer's hand.
- One-piece design reduces cost and installation time.
- Nyties feature a bent tip for ease of pickup and insertion around small bundles. V-shaped raised ridges on the tip provide a sure grip.
- Close, evenly spaced teeth permit fine adjustment—from .025" (0,6 mm) on the smallest Nyties to .063" (1,6 mm) on the largest.

Screw Mountable Nyties

- Molded-in screw hole mount provides one-piece mounting and bundling.
- Mounting screws not included.

Push Mountable Nyties

- Snap quickly into holes with only fingertip pressure.
- Provide one-piece mounting and bundling.
- Hold securely in panels up to 1/8" (3,2 mm) thick.



Heyco® Nytye® Nylon Cable Ties

PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS							
Max. Tensile Strength	Max. Bundle Diameter			Natural	UV Black		A Length		B Width		C Thickness		Min Bundle Diameter	
lbs. N	in. mm.						in. mm.		in. mm.		in. mm.		in. mm.	

Regular Nyties®

18	80	.75 1.50 2.00	19,1 38,1 50,8	3500 3503 3506	3502 3504 3507	NT 70 NT 70L NT 70E	3.80 6.25 8.00	97 159 203	.09 2,3		.05 1,1			
30	133	1.00	25,4	3510	3511	NT 90	5.20	132	.12	2,9				
40	178	1.25 2.00	31,8 50,8	3515 3850	3516 3851	NT 120 NT 170	5.67 8.25	144 210	.14 3,4		.06 .05	1,4 1,3	.06	1,6
50	222	1.75 3.00 4.00	44,4 76,2 101,6	3520 3525 3530	3521 3526 3531	NT 150 NT 250 NT 330	7.50 11.25 14.50	191 286 368	.19 4,8		.06 1,4			


Screw Mountable Nyties®

30	133	1.00	25,4	3550	-	MNT 90	5.50	140	.12	2,9	.05	1,1	4
40	178	1.25	31,8	3555	-	MNT 120	6.50	165	.14	3,4	.05	1,3	8
50	222	1.75	44,4	3560	-	MNT 150	8.00	203	.19	4,8	.06	1,4	10



Push Mountable Nyties®

40	180	1.42	36,0	-	3907	PWMS-155 HSB	6.23	158	.14	3,5	.05	1,2	.19	4,6
50	222	1.75	44,4	3904	-	PMT 150	8.00	203	.19	4,8	.06	1,4	.25	6,4


Standard color natural. UV Black at extra charge. Consult Heyco for Nyties in colors.




Regular Nyties



Screw Mountable Nyties



Push Mountable Nyties



Quick
Specs

Material
Certifications

Flammability Rating
Temperature Range

Nylon 6/6

Recognized under the Component Program of Underwriters' Laboratories File E54523

94V-2

32°F (0°C) to 185°F (85°C)