

1

International Components Corporation Quality Components since 1970

PIEZO ELECTRIC ALARM WITH INTERNAL CIRCUITRY



ROHS COMPLIANT

PART NUMBER: BRP2411P-12-CFS

SPECIFICATIONS:

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	3 ~ 15 VDC
MAX CURRENT:	10 mA
SOUND OUTPUT LEVEL:	90dB @30CM
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	3700 ± 500 Hz
OPERATING TEMPERATURE:	-30 TO +110 °C
TONE MODE:	CONTINUOUS
FRAME DIAMETER:	24.0 mm
FRAME DEPTH:	11.0 mm
MOUNTING DIMENSIONS:	15.0 mm

COMMENTS:

Wave Solderable and Washable Available in 17.5 mm Pin Spacing **DIMENSIONS:**



