

# International Components Corporation Quality Components since 1970

## PIEZO ELECTRIC ALARM WITH INTERNAL CIRCUITRY



# PART NUMBER: BRP2416P-12-C

#### **SPECIFICATIONS:**

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	3 ~ 20 VDC
MAX CURRENT:	10 mA
SOUND OUTPUT LEVEL:	85dB @30CM
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2800 ± 500 Hz
OPERATING TEMPERATURE:	-20 TO +70 °C
TONE MODE:	CONTINUOUS
FRAME DIAMETER:	23.8 mm
FRAME DEPTH:	16.0 mm
MOUNTING DIMENSIONS:	15.0 mm

### **DIMENSIONS:**

