

1

SELF-DRIVE PIEZO ELECTRIC



AVAILABLE ROHS COMPLIANT UPON REQUEST

PART NUMBER: BRP3408P-30

SPECIFICATIONS:

RATED VOLTAGE:	30 Vp-p
SOUND OUTPUT LEVEL:	95dB @ 30C
TERMINAL TYPE:	3 PINS
RESONANT FREQUENCY:	2500 ± 500 Hz
OPERATING TEMPERATURE:	-20 TO +60 °C
ELECTROSTATIC CAPACITY:	25,000 ± 30%
FRAME DIAMETER:	33.5 mm
FRAME DEPTH:	8.0 mm
MOUNTING DIMENSIONS:	See Diagram

