

1

## International Components Corporation Quality Components since 1970

## PIEZO SOUNDER WITH BUILT-IN CIRCUIT



**ROHS COMPLIANT** 

PART NUMBER: BRP4016L-12-CP

## **SPECIFICATIONS:**

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	3 ~ 24 VDC
MAX CURRENT:	18 mA
SOUND OUTPUT LEVEL:	100dB @ 10CM
TERMINAL TYPE:	2 LEADWIRES
RESONANT FREQUENCY:	2800 ± 300 Hz
OPERATING TEMPERATURE:	-20 TO +60 °C
TONE MODE:	INTERMITTENT: 1:1
FRAME DIAMETER:	40.0 mm
FRAME DEPTH:	16.0 mm
MOUNTING DIMENSIONS:	50.0 mm

## **DIMENSIONS:**

