

**PIEZO ELECTRIC ALARM WITH INTERNAL CIRCUITRY**



**ROHS COMPLIANT**

**PART NUMBER:**  
**BRP4535S-12-CP**

**SPECIFICATIONS:**

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	4 ~ 16 VDC
MAX CURRENT:	20 mA
SOUND OUTPUT LEVEL:	90dB @ 30CM
TERMINAL TYPE:	2 SCREW LUGS
RESONANT FREQUENCY:	2900 ± 500 Hz
OPERATING TEMPERATURE:	-20 TO +60 °C
TONE MODE:	INTERMITT: 0.8-1.2
FRAME DIAMETER:	43.5 mm
FRAME DEPTH:	34.5 mm
MOUNTING DIMENSIONS:	Panel Mount

**DIMENSIONS:**

