

1

International Components Corporation Quality Components since 1970

ELECTRO-ACOUSTIC TRANSDUCER



ROHS COMPLIANT

PART NUMBER: BRT1209L-01

SPECIFICATIONS:

RATED VOLTAGE:	1.5 VDC
OPERATING VOLTAGE:	1 ~ 2
MAX CURRENT:	30 mA
SOUND OUTPUT LEVEL:	80dB @ 10 cm
TERMINAL TYPE:	2 LEADWIRES
RESONANT FREQUENCY:	2048 Hz
OPERATING TEMPERATURE:	-20 TO +60°C
TONE MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	16 ± 4
COIL IMPEDANCE:	40
FRAME DIAMETER:	12.0 mm
FRAME DEPTH:	8.5 mm
MOUNTING DIMENSIONS:	3.0 mm

COMMENTS:

*VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY, **VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

