

# International Components Corporation Quality Components since 1970

## **ELECTRO-ACOUSTIC TRANSDUCER**



**ROHS COMPLIANT** 

PART NUMBER: BRT1209P-01-C

## **SPECIFICATIONS:**

RATED VOLTAGE:	1.5 VDC
OPERATING VOLTAGE:	1.2 ~ 3
MAX CURRENT:	30 mA
SOUND OUTPUT LEVEL:	70dB @ 10 cm
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2500 Hz
OPERATING TEMPERATURE:	-20 TO +70°C
TONE MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	NOT APPLIC
COIL IMPEDANCE:	WITH BUILT
FRAME DIAMETER:	12.0 mm
FRAME DEPTH:	9.5 mm
MOUNTING DIMENSIONS:	7.6 mm

### **COMMENTS:**

<sup>\*</sup>VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

<sup>\*\*</sup>VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

# **DIMENSIONS:**

