

International Components Corporation Quality Components since 1970

ELECTRO-ACOUSTIC TRANSDUCER



ROHS COMPLIANT

PART NUMBER: BRT1209P-12-C

SPECIFICATIONS:

12 VDC	
7 ~ 15	
30 mA	
80dB @ 10 cm	
2 PINS	
2300 Hz	
-20 TO +70°C	
CONTINUOUS	
N/A	
NOT APPLIC	
WITH BUILT	
12.0 mm	
9.5 mm	
7.6 mm	

COMMENTS:

^{*}VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

^{**}VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

DIMENSIONS:

