

# International Components Corporation Quality Components since 1970

## **ELECTRO-ACOUSTIC TRANSDUCER**



#### ROHS COMPLIANT AVAILABLE UPON REQUEST

PART NUMBER: BRT1209PF-05-RA

## **SPECIFICATIONS:**

of Edition Ideal	
RATED VOLTAGE:	5 VDC
OPERATING VOLTAGE:	4 ~ 8
MAX CURRENT:	40 mA
SOUND OUTPUT LEVEL:	85dB @ 10 cm
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2400 Hz
OPERATING TEMPERATURE:	-40 TO +85°C
TONE MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	45 ± 5
COIL IMPEDANCE:	80
FRAME DIAMETER:	12.0 mm
FRAME DEPTH:	9.5 mm
MOUNTING DIMENSIONS:	6.5 mm

#### **COMMENTS:**

<sup>\*</sup>VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

<sup>\*\*</sup>VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

# **DIMENSIONS:**

