

ELECTRO-ACOUSTIC TRANSDUCER



ROHS COMPLIANT

PART NUMBER:
BRT1615P-12-C

SPECIFICATIONS:

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	8 ~ 16
MAX CURRENT:	30 mA
SOUND OUTPUT LEVEL:	85dB @ 10 cm
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2200 Hz
OPERATING TEMPERATURE:	-20 TO +70°C
TONE MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	NOT APPLIC
COIL IMPEDANCE:	WITH BUILT
FRAME DIAMETER:	16.0 mm
FRAME DEPTH:	14.5 mm
MOUNTING DIMENSIONS:	7.6 mm

COMMENTS:

*VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

**VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

DIMENSIONS:

