

International Components Corporation Quality Components since 1970

ELECTRO-ACOUSTIC TRANSDUCER



ROHS COMPLIANT

PART NUMBER: BRT1615P-12

SPECIFICATIONS:


RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	6 ~ 18
MAX CURRENT:	40 mA
SOUND OUTPUT LEVEL:	85dB @ 10 cm
TERMINAL TYPE:	2 PINS
RESONANT FREQUENCY:	2048 Hz
OPERATING TEMPERATURE:	-20 TO +70°C
TONE MODE:	CONTINUOUS
PULSE RATE:	N/A
COIL RESISTANCE:	115 ± 12
COIL IMPEDANCE:	200
FRAME DIAMETER:	16.0 mm
FRAME DEPTH:	14.5 mm
MOUNTING DIMENSIONS:	7.6 mm

COMMENTS:

^{*}VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

^{**}VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

DIMENSIONS:



potting