ELECTRO-ACOUSTIC TRANSDUCER



ROHS COMPLIANT AVAILABLE UPON REQUEST

PART NUMBER: BRT2821P-12

SPECIFICATIONS:

12 VDC RATED VOLTAGE: OPERATING VOLTAGE: 9 ~ 15 MAX CURRENT: 40 mA SOUND OUTPUT LEVEL: 95dB @ 30 cm TERMINAL TYPE: 2 PINS RESONANT FREQUENCY: 2800 ± 200 OPERATING TEMPERATURE: -20 TO +60°C **CONTINUOUS** TONE MODE: PULSE RATE: N/A

COIL RESISTANCE:

COIL IMPEDANCE:

WITH BUILT

FRAME DIAMETER:

FRAME DEPTH:

MOUNTING DIMENSIONS:

NOT APPLIC

28.0 mm

20.0 mm


14.0 mm

COMMENTS:


*VALUE APPLYING RATED VOLTAGE (RESONANT FREQUENCY,

**VALUE APPLYING (RESONANT FREQUENCY, SINE WAVE, M

DIMENSIONS:



FREQUENCY RESPONSE:



**Note - Frequency is 2.8 KHz. + 0.2 KHz. from 3 to 8 VDC