

ELECTRONIC BUZZER



ROHS COMPLIANT

PART NUMBER:
BS2316L-24

SPECIFICATIONS:

RATED VOLTAGE:	24 VDC
OPERATING VOLTAGE:	10 ~ 27 VD
MAX CURRENT:	25 mA
SOUND OUTPUT LEVEL:	75 dB @ 30
TERMINAL TYPE:	2 LEADWIRE
RESONANT FREQUENCY:	400 ± 50 H
OPERATING TEMPERATURE:	-40 TO + 70°C
FRAME DIAMETER:	23.0 x 16.6 mm
FRAME DEPTH:	15.8 mm
MOUNTING DIMENSIONS:	27.0 mm

DIMENSIONS:

