

ELECTRONIC BUZZER



ROHS COMPLIANT UPON REQUEST

PART NUMBER:
BS2620FV-12

SPECIFICATIONS:

RATED VOLTAGE:	12 VDC
OPERATING VOLTAGE:	8 ~ 16 VDC
MAX CURRENT:	60 mA
SOUND OUTPUT LEVEL:	75 dB @ 100 cm
TERMINAL TYPE:	2 FAST-ON
RESONANT FREQUENCY:	400 ± 50 Hz
OPERATING TEMPERATURE:	-40 TO + 70°C
FRAME DIAMETER:	26.0 x 26.0 mm
FRAME DEPTH:	19.5 mm
MOUNTING DIMENSIONS:	32.0 mm

DIMENSIONS:

