

ELECTRONIC BUZZER



ROHS COMPLIANT

PART NUMBER:
BS2620PH-06-C

SPECIFICATIONS:

RATED VOLTAGE:	6 VDC
OPERATING VOLTAGE:	4 ~ 8 VDC
MAX CURRENT:	30 mA
SOUND OUTPUT LEVEL:	75 dB @ 100 cm
TERMINAL TYPE:	4 PINS
RESONANT FREQUENCY:	400 ± 50 Hz
OPERATING TEMPERATURE:	-40 TO + 70°C
FRAME DIAMETER:	26.0 x 26.0 mm
FRAME DEPTH:	19.5 mm
MOUNTING DIMENSIONS:	19.0 x 9.5 mm

DIMENSIONS:

