

ELECTRONIC BUZZER



ROHS COMPLIANT UPON REQUEST

PART NUMBER:
BS2620PH-24-C

SPECIFICATIONS:

| | |
|------------------------|----------------|
| RATED VOLTAGE: | 24 VDC |
| OPERATING VOLTAGE: | 20 ~ 28 VD |
| MAX CURRENT: | 20 mA |
| SOUND OUTPUT LEVEL: | 75 dB @ 100 cm |
| TERMINAL TYPE: | 4 PINS |
| RESONANT FREQUENCY: | 400 ± 50 Hz |
| OPERATING TEMPERATURE: | -40 TO + 70°C |
| FRAME DIAMETER: | 26.0 x 26.0 mm |
| FRAME DEPTH: | 19.5 mm |
| MOUNTING DIMENSIONS: | 19.0 x 9.5 mm |

DIMENSIONS:

